


DECON95™

Disinfects N95 Facepiece Forming Respirators (FFRs) with levels of ultraviolet energy shown to inactivate coronavirus

- Stable Microwave Powered UVC Output
- Field Deployable, Benchtop Unit
- Industrial grade for continuous use
- Conveyorized for controlled, high throughput



Max Opening Height: 5.5 in

Belt Width: 12"

Daily N95 Respirator Capacity: over 4,000

UVC Dose at belt: over 1,000 mJ/cm²



	Size H x W x D (in)	Weight (lb)	Voltage (VAC)	Max Current (A)
Lamp	19.8 x 11.1 x 6.8	28	220 (208-240)	15
Power Supply (not shown)	7.5 x 13.7 x 16	71		
Conveyor Assembly	45.8 x 42.4 x 26 w/ lamp installed (45.8 x 54.5 x 26 w/ light guards)	77	120	2.5

Patent Pending